One-piece elongated toilet with skirted trapway, 1.28

gpf

K-46006

Features

- One-piece toilets integrate the tank and bowl into a seamless, easy-to-clean design
- Compact elongated bowl offers added comfort while occupying the same space as a round-front bowl
- Comfort Height® feature offers chair-height seating that makes sitting down and standing up easier for most adults
- 1.28 gpf (4.8 lpf)
- 12" x 9-1/2" (305 mm x 241 mm) water surface
- Concealed trapway facilitates easy cleaning and enhances design

Installation

- Floor-mount
- Standard 12" (305 mm) rough-in





Codes/Standards

ASME A112.19.2/CSA B45.1 DOE - Energy Policy Act 1992 EPA WaterSense® California Energy Commission (CEC) IAPMO Certification

KOHLER® One-Year Limited Warranty


See website for detailed warranty information.



One-piece elongated toilet with skirted trapway, 1.28

gpf

K-46006



Technical Information

All product dimensions are nominal.

Toilet type: Floor-mount

Waste Outlet: Floor
Bowl shape: Elongated
Flush type: Pressure Lite
Trap passageway: 1-15/16" (49 mm)

Water surface size: 11-1/2" x 10-3/16" (293 mm x 258 mm)

Rim to water 5-1/4" (134 mm)

surface:

Rough-in: 12" (305 mm)

Fixture Supply Requirements

Min static pressure: 50 psi (344.7 kPa)
Max static pressure: 80 psi (551.6 kPa)
Min flow rate: 6.5 gpm (24.6 lpm)

Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.