



Tresham®
Elongated toilet bowl
K-4799

Features

- Elongated bowl offers added room and comfort
- Comfort Height® feature offers chair-height seating that makes sitting down and standing up easier for most adults
- Combines with the K-4899 tank to create a complete K-3950 Tresham toilet
- Coordinates with other products in the Tresham collection
- 2-1/8" (54 mm) fully glazed trapway

Installation

- Seat sold separately
- Standard 12" (305 mm) rough-in

Recommended Products/Accessories

K-4899 Toilet tank, 1.28 gpf
K-23726 Drain treatment



Codes/Standards

ASME A112.19.2/CSA B45.1
IAPMO Certification

**KOHLER® Toilets and Seats Limited
Warranty**

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	0	White
---	---	-------

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Trap passageway:	2-1/8" (54 mm)
Rough-in:	12" (305 mm)
Seat-mounting holes:	5-1/2" (140 mm)

Notes

Install this product according to the installation instructions.