

Features

- Two-function pull-down sprayhead allows you to switch from aerated stream to Sweep™ spray
- Aerated flow delivers a smooth, steady stream of water
- Sweep™ spray creates a wide, forceful blade of water for superior cleaning
- DockNetik™ secure docking system locks sprayhead into place when not in use
- Quiet nylon retractable hose
- 360° swivel spout
- 9.45 inch (240 mm) spout height
- 9.02 inch (229 mm) spout reach
- Single handle provides on/off activation, volume, and temperature control
- Red/blue indexing on handle
- 1.5 gpm (5.5 lpm) maximum flow rate at 43.5 psi (3.0 bar)
- Includes 10.5 inch (267 mm) escutcheon plate and refillable 16 fluid ounce (473 mL) soap dispenser
- Space-saving soap dispenser keeps your kitchen sink clean and clutter-free

Material

- Durable material construction

Installation

- Deck-mount
- Installs with 1-, 2-, 3-, or 4- hole sink (escutcheon plate included)



Codes/Standards

None Applicable

KOHLER® India Faucet Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	VS	Vibrant® Stainless
---	----	--------------------



Technical Information

All product dimensions are nominal.

Drain included: No

Notes

Install this product according to the installation guide.