



**Delafield®**

33" top-mount double-bowl kitchen sink  
**K-5817-4**

### Features

- 33" (838 mm) minimum base cabinet width
- Double-equal bowls
- 8" (203 mm) depth
- Three faucet holes and one accessory hole to the right

### Material

- KOHLER® enameled cast iron

### Installation

- Top-mount

### Recommended Products/Accessories

- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23725 Cast iron cleaner

### Optional Products/Accessories

- K-11352 Disposal Flange with Stopper
- K-9000 P-Trap



### Codes/Standards

- ASME A112.19.1/CSA B45.2
- IAPMO Certification

**KOHLER® Enameled Cast Iron  
Kitchen and Bathroom Sink Lifetime  
Limited Warranty**

See website for detailed warranty information.


1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada

1-4-2025 20:14 - US/CA

THE BOLD LOOK  
OF **KOHLER®**



#### Technical Information

All product dimensions are nominal.

Basin configuration: Equal Bowls

Min. base cabinet width: 33" (838 mm)

Bowl area (Left): Length: 15" (381 mm)  
Width: 14" (356 mm)  
Bowl depth: 8" (203 mm)

Bowl area (Right): Length: 15" (381 mm)  
Width: 14" (356 mm)  
Bowl depth: 8" (203 mm)

Number of deck holes: 4

Faucet hole(s): 1-3/8" (35 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1040401-7, required, included

#### Notes

Install this product according to the installation instructions.