



33" top-mount double-bowl kitchen sink

K-5818-1

Features

- 36" minimum base cabinet width
- Double-equal bowls
- 9" (229 mm) depth provides generous workspace
- Single faucet hole
- Rear drain placement increases cabinet storage space underneath sink

Material

KOHLER® enameled cast iron

Installation

Top-mount

Recommended Products/Accessories

K-5133 Left-Bowl Sink Rack
K-5135 Right-Bowl Sink Rack
K-8801 Sink drain and strainer with tailpiece
K-8799 Sink drain and strainer basket
K-23726 Drain treatment
K-23725 Cast iron cleaner
1411886 Undermount sink kit 23"

Optional Products/Accessories

K-11352 Disposal Flange with Stopper K-9000 P-Trap



Codes/Standards

ASME A112.19.1/CSA B45.2 IAPMO Certification

KOHLER® Enameled Cast Iron Kitchen and Bathroom Sink Lifetime Limited Warranty

See website for detailed warranty information.


Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Biscuit
	7	Black Black™



33" top-mount double-bowl kitchen sink K-5818-1



Technical Information

All product dimensions are nominal.

Basin configuration: Equal Bowls

Min. base cabinet 33" (838 mm)

width:

Bowl area (Left): Length: 14-1/8" (359 mm)

Width: 16-1/4" (413 mm) Bowl depth: 9" (229 mm)

Bowl area (Right): Length: 14-1/8" (359 mm) Width: 16-1/4" (413 mm)

1

Bowl depth: 9" (229 mm)

Number of deck

holes:

Faucet hole(s): 1-3/8" (35 mm)
Drain hole: 3-7/8" (98 mm)

Template: 1125670-7, required, included

Notes

Install this product according to the installation instructions.

NOTICE: The countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by the Kohler Co. (Call 1-800-4-KOHLER.) Kohler Co. is not responsible for cut-out errors when the incorrect cut-out template is used.

