



Delafield®
tile-in/metal frame double-equal kitchen sink
K-5950-4

Features

- 36" minimum base cabinet width
- Double-equal bowls
- 8" (203 mm) depth
- Three faucet holes and one accessory hole to the right

Material

- KOHLER® enameled cast iron

Installation

- Tile-in or top-mount

Recommended Products/Accessories

- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23725 Cast iron cleaner

Optional Products/Accessories

- K-11352 Disposal Flange with Stopper
- K-9000 P-Trap




Codes/Standards

- ASME A112.19.1/CSA B45.2
- IAPMO Certification

**KOHLER® Enameled Cast Iron
Kitchen and Bathroom Sink Lifetime
Limited Warranty**

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Basin configuration:	Equal Bowls
Min. base cabinet width:	36" (914 mm)
Bowl area (Left):	Length: 14" (356 mm) Width: 15" (381 mm) Bowl depth: 8" (203 mm)
Bowl area (Right):	Length: 14" (356 mm) Width: 15" (381 mm) Bowl depth: 8" (203 mm)
Number of deck holes:	4
Faucet hole(s):	1-3/8" (35 mm)
Drain hole:	3-5/8" (92 mm)

Notes

Install this product according to the installation instructions.