



Mayfield™
25" top-mount single-bowl kitchen sink
K-5964-1

Features

- 27" (686 mm) minimum base cabinet width
- Single bowl
- 7-3/4" (197 mm) depth
- Single faucet hole
- Constructed of KOHLER® Enameled Cast Iron.

Material

- KOHLER® enameled cast iron

Installation

- Top-mount

Recommended Products/Accessories

- K-6003 Sink Rack
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23725 Cast iron cleaner

Optional Products/Accessories

- K-11352 Disposal Flange with Stopper
- K-9000 P-Trap



Codes/Standards




ASME A112.19.1/CSA B45.2


**KOHLER® Enameled Cast Iron
Kitchen and Bathroom Sink Lifetime
Limited Warranty**

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|---|------|--------------|
|  | 0 | White |
|  | 96 | Biscuit |
|  | 7 | Black Black™ |



Technical Information

All product dimensions are nominal.

| | |
|----------------------|--|
| Basin configuration: | Single Bowl |
| Cutout: | Top-mount, 23-3/4" x 20-3/4" (603 mm x 527 mm) with 1" (25 mm) radius corners |
| Bowl area (Only): | Length: 22" (559 mm) Width: 15" (381 mm) Bowl depth: 8" (203 mm) Water depth: 7-3/4" (197 mm) |
| Drain hole: | 3-5/8" (92 mm) |
| Template: | 1031341-7, required, included |

Notes

Install this product according to the installation instructions.