



Gimlet™

Top-mount Bar Sink

K-6015-2

Features

- 15-inch minimum base cabinet width.
- Single bowl.
- 5-1/2" depth.
- Two faucet holes.
- Small size fits compact spaces.

Material

- Acrylic.

Installation

- Wall-mount or top-mount.

Recommended Products/Accessories

K-8801 Sink Strainer
K-8799 Sink Strainer
K-23726 Drain treatment
K-23723 Faucet cleaner

Optional Products/Accessories

K-11352 Disposal Flange with Stopper
K-9000 P-Trap



ADA

Codes/Standards

CSA B45.5/IAPMO Z124
ADA
ICC/ANSI A117.1


KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Biscuit
	47	Almond
	33	Mexican Sand™
	7	Black Black™



Technical Information

All product dimensions are nominal.

Bowl configuration: Single

Installation: Top-mount

Min. base cabinet width: 15" (381 mm)

Bowl area:
Length: 11-1/2" (292 mm)
Width: 9-1/2" (241 mm)
Bowl depth: 5-1/2" (140 mm)
Water depth: 5-1/2" (140 mm)

Number of deck holes: 2

Faucet hole(s): 1-3/8" (35 mm)

Drain hole: 3-1/2" (89 mm)

Template: 102519-7, required, included

Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.

ADA permits a parallel approach to wet bars.