

Features

- 8" (203 mm) widespread faucet holes
- 1/4-turn full brass ceramic valve
- Includes Coralais® showerhead with 1.75 gal/min (6.6 l/min) maximum flow rate [max at 60 psi (4.14 bar)]; 30% more water saving than 2.5 gpm showerheads
- 2-7/16" vandal-resistant metal lever handles
- Drain sold separately

Material

- Solid-brass construction for durability and reliability



Codes/Standards

None Applicable


KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome



Technical Information

All product dimensions are nominal.

Spout:

Handle clearance: 2-7/16" (62 mm)

Shower/Rainhead rated max flow: 1.75 gal/min (6.6 l/min)

Notes

For use with automatic compensating valves rated at 1.35 gal/min (5.1 l/min) or less.

Install this product according to the installation instructions.