

### Features


- 8" (203 mm) widespread faucet holes
- 1/4-turn full brass ceramic valve
- Includes Coralais<sup>®</sup> showerhead with 1.75 gal/min (6.6 l/min) maximum flow rate [max at 60 psi (4.14 bar)]; 30% more water saving than 2.5 gpm showerheads
- 2-7/16" vandal-resistant metal lever handles
- Drain sold separately

### Material

- Solid-brass construction for durability and reliability

### Recommended Products/Accessories

K-23723 Faucet cleaner



### Codes/Standards

None Applicable



### KOHLER<sup>®</sup> One-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome



### Technical Information

All product dimensions are nominal.

Drain included: No

### Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

### Showerhead/Body Spray:

Rated maximum flow: 1.75 gal/min (6.6 l/min)

### Notes

For use with automatic compensating valves rated at 1.35 gal/min (5.1 l/min) or less.

Install this product according to the installation instructions.