



**Whitehaven®**  
 35-3/4" undermount single-bowl farmhouse kitchen  
 sink  
**K-6489**

**Features**

- Fits minimum 36" (914 mm) apron sink base cabinet
- Single bowl
- 9" (229 mm) depth provides generous workspace
- Self-Trimming® apron overlaps cabinet face for easy installation and beautiful results
- Bowl slopes toward drain to minimize water pooling
- Offset drain increases workspace in the sink and storage space underneath
- Sink drain with strainer sold separately

**Material**

- KOHLER® enameled cast iron
- Acid-resistant enamel finish

**Installation**

- Cutout templates included
- Undermount

**Required Products/Accessories**

K-6639 Sink racks for 36" Whitehaven® (Qty 2)

or

K-8799 Sink drain and strainer basket (Qty 2)

**Recommended Products/Accessories**

K-23725 Cast iron cleaner

K-23726 Drain treatment

**Optional Products/Accessories**

K-9000 P-Trap



**Codes/Standards**

ASME A112.19.1/CSA B45.2


**KOHLER® Enameled Cast Iron  
 Kitchen and Bathroom Sink Lifetime  
 Limited Warranty**

See website for detailed warranty information.

**Available Colors/Finishes**

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	FF	Sea Salt™
	96	Biscuit
	NY	Dune
	95	Ice™ Grey
	58	Thunder™ Grey
	7	Black Black™
	TRF	Truffle
	GRL	Grey Lavender
	17	Teal
	34	Fresh Green
	42	Aspen Green



## Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 36" (914 mm)

Bowl area (Only): Length: 30-3/4" (781 mm)  
 Width: 18-1/16" (459 mm)  
 Bowl depth: 9" (229 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1156910-7, required, included  
 1157001, required, included

## Notes

Install this product according to the installation instructions.

**IMPORTANT!** The distance from the top edge of the cabinet to the top of the cabinet door must be at least 9" (229 mm) to install this sink.