



18-1/2" top-/undermount single-bowl bar sink **K-6565**

Features

- 21" (533 mm) minimum base cabinet width
- Single round bowl
- 8" (203 mm) depth

Material

KOHLER® enameled cast iron

Installation

Top-mount or undermount

Recommended Products/Accessories

K-8801 Sink drain and strainer with tailpiece K-8799 Sink drain and strainer basket K-23726 Drain treatment K-23725 Cast iron cleaner

Optional Products/Accessories

K-11352 Disposal Flange with Stopper

Included Components

52047 Clamp Accessory Pack, 4 Ea.



ADA

Codes/Standards

ASME A112.19.1/CSA B45.2 ADA ICC/ANSI A117.1 IAPMO Certification

KOHLER® Enameled Cast Iron Kitchen and Bathroom Sink Lifetime Limited Warranty

See website for detailed warranty information.


Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	FF	Sea Salt™
	96	Biscuit
	NY	Dune
	95	Ice™ Grey
	58	Thunder™ Grey
	7	Black Black™
	TRF	Truffle
	17	Teal
	42	Aspen Green
	34	Fresh Green



18-1/2" top-/undermount single-bowl bar sink **K-6565**



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet 21" (533 mm)

width:

Bowl area (Only): Length: 15" (381 mm)

Width: 15" (381 mm)

Bowl depth: 8" (203 mm)

Drain hole: 3-5/8" (92 mm)

Template: 112355-7, required, included

Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.

ADA permits a parallel approach to wet bars.