



**Langlade®**  
Smart Divide® 33" undermount double-bowl kitchen  
sink  
**K-6626-6U**

### Features

- 36" minimum base cabinet width
- Double-equal bowls
- 9" (229 mm) depth provides generous workspace
- Six oversized faucet holes
- Oversized holes allow for easy installation of faucets and accessories
- Smart Divide® feature offers a lower bowl divider that increases workspace versatility

### Material

- KOHLER® enameled cast iron

### Installation

- Undermount
- Undermount installation kit not included

### Recommended Products/Accessories

- K-5180 Right-bowl sink rack
- K-5182 Left-bowl sink rack
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-11352 Disposal Flange with Stopper
- K-9000 P-Trap
- 1411886 Undermount sink kit 23"
- K-23726 Drain treatment
- K-23725 Cast iron cleaner




### Codes/Standards

ASME A112.19.1/CSA B45.2  
IAPMO Certification

### **KOHLER® Enameled Cast Iron Kitchen and Bathroom Sink Lifetime Limited Warranty**

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Basin configuration: Equal Bowls  
Min. base cabinet width: 36" (914 mm)

Bowl area (Left): Length: 15" (381 mm)  
Width: 18-3/8" (467 mm)  
Bowl depth: 9" (229 mm)

Bowl area (Right): Length: 15" (381 mm)  
Width: 18-3/8" (467 mm)  
Bowl depth: 9" (229 mm)

Number of deck holes: 6

Faucet hole(s): 2-3/8" (60 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1043754-7, required, included

## Notes

Install this product according to the installation instructions.