



River Falls™

25" undermount single-bowl utility sink
K-6657-4U

Features

- 27" (686 mm) minimum base cabinet width
- Single bowl
- 14-1/4" depth provides generous workspace
- Four oversized faucet holes
- Oversized holes allow for easy installation of faucets and accessories
- Sink drain with strainer sold separately

Material

- KOHLER® enameled cast iron

Installation

- Undermount installation kit not included
- Undermount

Recommended Products/Accessories

- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-11352 Disposal Flange with Stopper
- K-9000 P-Trap
- 1411886 Undermount sink kit 23"
- K-23726 Drain treatment
- K-23725 Cast iron cleaner




Codes/Standards

ASME A112.19.1/CSA B45.2

KOHLER® Enameled Cast Iron Kitchen and Bathroom Sink Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 27" (686 mm)

Bowl area: Length: 21-1/2" (546 mm)
Width: 14-3/4" (375 mm)
Bowl depth: 14-1/4" (362 mm)

Number of deck holes: 4

Faucet hole(s): 2-3/8" (60 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1079984-7, required, included

Notes

Install this product according to the installation instructions.