



Fluence® | K-702219-L

37"-40" W x 76" H sliding shower door with 1/4"-thick Crystal Clear glass

Features

- Gently curved inside and outside towel bars complete the look of this door
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)
- Tempered glass ensures enhanced safety and durability



DISCONTINUED



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

7-29-2026 20:36 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

ANSI Z97.1 (Tempered Glass)
CAN/CGSB-12.1
CPSC 16CFR 1201

Technical Information

All product dimensions are nominal.

Base-To-Wall Radius – 1/2" (13 mm)
Maximum:
Shower Ledge Minimum Flat: 2-1/8" (54 mm)
Shower Wall Minimum Flat: 3-1/8" (80 mm)

Material

- Frameless, 1/4" (6 mm) thick Crystal Clear tempered glass

Technology


- Continuous door panel guide mechanism for smooth, quiet sliding action

Warranty

See website for detailed warranty information.

KOHLER® Bath and Shower Doors Ten-Year Limited
Warranty





Installation

- Out-of-plumb adjustability simplifies installation
- Not for use in hospitality

Installation Notes

Install this product according to the installation instructions.

The vertical opening should be a minimum of 77-3/4" (1975 mm) to allow for installation clearance.

