



Premise™ | K-702471-8L

56-5/8"-59-5/8" W x 76-3/16" H sliding shower door with 5/16"-thick Crystal Clear glass

Features

- Premium stainless steel roller design allows for effortless opening and closing of the moving panel
- Controlled Close® innovative soft-close with double-dampening technology brings door to a secure close
- Removable center guide for easy cleaning of surrounding surfaces and bottom threshold
- Frameless design emphasizes glass and creates a sleek, minimalist look
- Back-to-back 15-1/8" (384 mm) vertical handles
- Tempered glass ensures enhanced safety and durability
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)
- Smooth, easy-to-clean wall jambs
- Shower door configuration consists of one sliding panel and one stationary panel
- Coordinates with other products in the Premise™ collection



Available Colors/Finishes

Color tiles intended for reference only.

- SHP Bright Polished Silver
- 2MB Vibrant Brushed Moderne Brass



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

8-11-2026 11:01 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

ANSI Z97.1 (Tempered Glass)

CAN/CGSB-12.1

CPSC 16CFR 1201

Technical Information

All product dimensions are nominal.

Base-To-Wall Radius – 1/2" (13 mm)

Maximum:

Shower Ledge Minimum Flat: 2-3/16" (56 mm)

Shower Wall Minimum Flat: 1-1/4" (32 mm)

Weight: 142 lbs (64.4 kg)

Material

- Frameless, heavy 5/16" (8 mm) thick Crystal Clear tempered glass
 - Anodized aluminum prevents rust and corrosion
-

Warranty

See website for detailed warranty information.

KOHLER® Bath and Shower Doors Ten-Year Limited
Warranty




1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

8-11-2026 11:01 - US-CA



Installation

- Fits opening widths 56-5/8" – 59-5/8" (1438 –1514 mm)
- 76-1/8" (1934 mm) high, with a lofty 74-7/16" (1891 mm) minimum head clearance
- 3" (76 mm) width adjustment
- 3/8" (10 mm) out-of-plumb adjustability on each side simplifies installation
- Door can be installed to open to the left or right to suit your bathroom layout
- For residential use only
- Not for use in hospitality

Installation Notes

Install this product according to the installation instructions.

The vertical opening should be a minimum of 79-1/16" (2008 mm) to allow for installation clearance.

