



Pinstripe® | K-705718-L

30-1/4"-32-3/4" W x 72-1/4" H pivot shower door with 1/2"-thick Crystal Clear glass

Features

- Frameless, 1/2" (12 mm) thick Crystal Clear tempered glass
- Includes sidelite panel
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)
- Includes glass, handle, and hardware components
- Coordinates with Pinstripe faucets, accessories, and showering components to complete your bathroom
- Tempered glass ensures enhanced safety and durability



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

9-03-2026 04:02 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

ANSI Z97.1 (Tempered Glass)

CAN/CGSB-12.1

CPSC 16CFR 1201

Technical Information

All product dimensions are nominal.

Base-To-Wall Radius – 3/8" (10 mm)
Maximum:

Included Combo Skus

- K-705763 Shower door assembly kit (glass and handle not included)
 - K-705755-L Glass panel and sidelite for 30" - 33" door
 - K-705768 14" pivot shower door handle
-

Technology

- Stainless steel and brass fasteners prevent rust and corrosion
-

Warranty

See website for detailed warranty information.

KOHLER® Bath and Shower Doors Ten-Year Limited
Warranty




1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

9-03-2026 04:02 - US-CA



Installation

- Out-of-plumb adjustability simplifies installation
- Door can be installed to open to the left or right to suit your bathroom layout
- Not for use in hospitality
- For residential use only

Installation Notes

Install this product according to the installation instructions.

The vertical opening should be a minimum of 74-1/4" (1886 mm) to allow for installation clearance.

