

Torsion® | K-706091-L

57-1/2"-59-1/16" W x 77" H sliding shower door with 5/16"-thick Crystal Clear glass

Features

- Includes a 36" (914 mm) wide glass return panel to create a corner enclosure
- Left-hand door slides open, fixed panel on left
- 11" geometric handle on both sides of the glass has a solid, heavy feel
- Ultra-low threshold (9/16") for easy entry and exit
- Seals provide excellent water containment
- Door catch closes door securely
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)
- No exposed screws for sleek, contemporary look



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
9-03-2026 05:00 - US-CA

THE BOLD LOOK
OF **KOHLER®**

Codes/Standards

ANSI Z97.1 (Tempered Glass)
CAN/CGSB-12.1
CPSC 16CFR 1201

Technical Information

All product dimensions are nominal.

Base-To-Wall Radius – 1" (25 mm)
Maximum:

Material

- Frameless, heavy 5/16" (8 mm) thick Crystal Clear tempered glass
- Anodized aluminum prevents rust and corrosion

Included Combo Skus

- K-706108-L 57-1/2"-59-1/16" W x 77" H sliding shower door with 5/16"-thick Crystal Clear glass
- K-706026-L 36" return panel

Recommended Products/Accessories


1296808 Torsion Filler Jamb, Door
1296809 Torsion Filler Jamb, Return Panel

Warranty

See website for detailed warranty information.

KOHLER® Bath and Shower Doors Ten-Year Limited
Warranty





Installation

- Sliding shower door
- For 48" x 36" corner installation
- Preassembled frame requires no cutting during installation
- 3/4" (19 mm) width adjustability on each wall jamb, offering 1-1/2" (25 mm) total adjustability
- Roller system adjustability for out-of-plumb fine-tuning
- Not for use in hospitality
- For residential use only

Installation Notes

Install this product according to the installation instructions.

The vertical opening should be a minimum of 80" (2032 mm) to allow for installation clearance.

