

Aerie® | K-706134-L

57-1/16"-59-7/16" W x 75" H sliding shower door with 5/16"-thick Crystal Clear glass

Features

- Includes a 36" (914 mm) wide glass return panel to create a corner enclosure
- 6-3/4" (171 mm) vertical handle on both sides of the glass
- Low, 1 3/4" (44 mm) threshold for easy entry and exit
- Seals provide excellent water containment
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)
- No exposed screws for sleek, contemporary look
- Includes K-706147-L sliding door and K-K-706152-L return panel



Codes/Standards

ANSI Z97.1 (Tempered Glass)
CAN/CGSB-12.1
CPSC 16CFR 1201

Warranty

See website for detailed warranty information.

KOHLER® Bath and Shower Doors Ten-Year Limited
Warranty

Technical Information

All product dimensions are nominal.

Base-To-Wall Radius – 1" (25 mm)
Maximum:

Material

- Frameless, heavy 5/16" (8 mm) thick Crystal Clear tempered glass

Included Combo Skus

- K-706152-L 34-1/16"-35-1/4" W x 75" H pivot shower door with 5/16"-thick Crystal Clear glass
- 706147-ML SKYLINE SLIDING DOOR MOVING PANEL 1500MM
- 706147-FL SKYLINE SLIDING DOOR FIXED PANEL 1500MM


Recommended Products/Accessories

1296810 Aerie® Filler Jamb

Technology

- Premium, quick-release double rollers on top and bottom for quality feel and operation
- Full-length magnetic strip keeps door firmly closed





Installation

- Sliding shower door
- For 60" x 36" (1524 x 914 mm) alcove installation
- Door can be installed to open to the left or right to suit your bathroom layout
- Twist & Lock wall jamb system locks into place with no cutting required
- 1-3/16" (30 mm) width adjustability on each wall jamb, offering 2-3/8" (60 mm) total adjustability
- Adjustable double rollers allow for out-of-plumb fine-tuning
- Not for use in hospitality
- For residential use only

Installation Notes

Install this product according to the installation instructions.

The vertical opening should be a minimum of 78" (1981 mm) to allow for installation clearance.

