



Cursiva™ | K-707628-8L

45"-47-1/2" W x 71-5/8" H pivot shower door with 5/16"-thick Crystal Clear glass

Features

- Innovative L- bracket secures the fixed panel in place and gives it a sturdy feel while also being unobtrusive to the showering space
- SealNetik™ full-length magnetic seal keeps door firmly closed, providing excellent water containment
- Full-length hinge system provides extra stability, safety, and smooth operation
- Frameless design emphasizes glass and creates a sleek, minimalist look
- Back-to-back 11-7/8" (301 mm) vertical shower door pulls
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)
- Coordinates with other products in the Cursiva collection



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
8-11-2026 11:00 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

ANSI Z97.1 (Tempered Glass)

CAN/CGSB-12.1

CPSC 16CFR 1201

Technical Information

All product dimensions are nominal.

Base-To-Wall Radius – 3/8" (10 mm)

Maximum:

Shower Ledge Minimum Flat: 1-3/4" (44 mm)

Shower Wall Minimum Flat: 6-1/16" (154 mm)

Weight: 100 lbs (45.4 kg)

Material

- Frameless, heavy 5/16" (8 mm) thick Crystal Clear tempered glass
 - Anodized aluminum prevents rust and corrosion
-

Warranty

See website for detailed warranty information.

KOHLER® Bath and Shower Doors Ten-Year Limited
Warranty




1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

8-11-2026 11:00 - US-CA



Installation

- 71-5/8" (1819 mm) high, with no minimum head clearance restriction
- Fits opening widths 45"-47-1/2" (1143-1207 mm)
- Requires 2" (51 mm) minimum threshold depth
- Requires minimum of 5-1/2" (140 mm) flat wall on fixed-panel side to mount L-bracket
- Shower glass mounting hardware and L-bracket must be attached to structural wall
- 3/8" (10 mm) out-of-plumb adjustability on each side simplifies installation
- Door can be installed to open to the left or right to suit your bathroom layout
- For residential use only
- Not for use in hospitality

Installation Notes

Install this product according to the installation instructions.

The vertical opening should be a minimum of 77-5/8" (1972 mm) to allow for installation clearance.

