

## Features

- Single Lever handle allows for on/off activation, volume, and temperature control
- Aerated flow
- 3.85 inch (98 mm) spout reach
- 3.5 inch (89 mm) spout height
- 3.69 gpm (14.0 lpm) maximum flow rate at 43.5 psi (3.0 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with other products in the Aleo™ collection
- Drain sold separately

## Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

## Installation

- For single-hole installation
- Preattached flexible supply lines simplify installation



## Codes/Standards




None Applicable


## KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	BV	Vibrant® Brushed Bronze
	RGD	Vibrant Rose Gold



## Technical Information

All product dimensions are nominal.

Drain included: No

Drain with overflow: No

## Notes

Install this product according to the installation guide.