

# KOHLER<sup>®</sup> Faucets

Single-handle bathroom sink faucet with lever handle,  
6.8 lpm  
**K-72275K-4**

## Features

- Single lever handle allows for both on/off activation and temperature setting
- 4-11/16" (101 mm) spout reach
- 3-1/2" (88 mm) spout height
- 1.8 gpm (6.8 lpm) maximum flow rate at 45 psi (3.1 bar)
- Aerated flow delivers a smooth, steady stream of water
- Red/blue indexing
- Includes valve
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- Includes pop-up drain
- Part of the Aleo bathroom faucet and showering collection
- G 3/8" connection

## Material


- Premium metal construction for durability and reliability
- KOHLER<sup>®</sup> finishes resist corrosion and tarnishing

## Installation

- Deck-mount
- For single-hole installation
- Flexible supply lines simplify installation

## Recommended Products/Accessories

K-23726 Drain treatment  
K-23723 Faucet cleaner




## Codes/Standards

General Acceptance (GA)

## KOHLER<sup>®</sup> Faucet Lifetime Limited Warranty

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

### Faucet:

Flow rate: 1.84 gal/min (7 l/min)

Pressure: 45 psi (3.1 bar)

Drain included: Yes

Drain with overflow: Yes

### Spout:

Spout reach: 4" (101 mm)

## Notes

Install this product according to the installation instructions.