

## Features

- Single Lever handle allows for on/off activation, volume, and temperature control
- 3.5 inch (89 mm) spout height
- 3.85 inch (98 mm) spout reach
- Aerated flow
- 1.0 gpm (3.8 lpm) maximum flow rate at 60 psi (4.14 bar)
- Includes pop-up drain with lift rod
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with other products in the Aleo™ collection

## Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

## Installation


- For single-hole installation
- Preattached flexible supply lines simplify installation



## Codes/Standards

None Applicable

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Faucet flow rate: 1 gal/min (3.8 l/min)

Drain included: Yes

### Notes

Install this product according to the installation instructions.