

### Features


- Features integrated 35 mm mixing valve
- Single lever handle allows for both volume and temperature control
- 4.22 gpm (16.0 lpm) maximum bath faucet flow rate at 45 psi (3.1 bar)
- Diverter spout
- Includes Awaken™ multifunction handshower, holder, and 60" (1524 mm) hose
- Advanced spray engine provides three alternate experiences: wide coverage, intense drenching, and targeted spray
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Thumb tab allows for a smooth transition between sprays
- 2.11 gpm (8.0 lpm) maximum handshower flow rate at 80 psi (5.5 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Part of the Aleo bathroom faucet and showering collection

### Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation



- Wall-mount
- G 1/2 inlet connection



### Codes/Standards

General Acceptance (GA)

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Drain included: No

### Notes

Install this product according to the installation instructions.