

Features

- Single Lever handle allows for on/off activation, volume, and temperature control
- Integrated diverter lets you toggle between two water outlets
- Laminar flow
- 6.5 gpm (24.6 lpm) maximum bath faucet flow rate at 45 psi (3.1 bar)
- Advanced spray engine provides three alternate experiences: wide coverage, intense drenching, and targeted spray
- Thumb tab allows for a smooth transition between sprays
- 2.38 gpm (9.0 lpm) maximum handshower flow rate at 80 psi (5.5 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Includes flexible G 1/2 supply hoses for easy installation

Material

- Brass
- KOHLER finishes resist corrosion and tarnishing

Installation


- Deck-mount



Codes/Standards

None Applicable

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet flow rate: 6.5 gal/min (24.6 l/min)

Handshower rated max flow: 2.5 gal/min (9.5 l/min)

Notes

Install this product according to the installation instructions.