

Features

- Tall height is ideal for vessel-style sinks
- Single lever handle allows for on/off activation, volume, and temperature control
- 6.22 inch (158 mm) spout reach
- 8.31 inch (211 mm) spout height
- 3.69 gpm (14.0 lpm) maximum flow rate at 43.5 psi (3.0 bar)
- Aerated flow delivers a smooth, steady stream of water
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For single-hole installation
- G 1/2 (13 mm) inlet connection
- Flexible supply lines simplify installation



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	RGD	Vibrant Rose Gold



Technical Information

All product dimensions are nominal.

Drain included: No

Notes

Install this product according to the installation guide.