

### Features

- Showerhead features contemporary design
- 1.75 gpm (6.6 lpm) showerhead flow rate
- Spray nozzles cover full area of 3-9/16" (90 mm) sprayhead
- Full coverage spray produces an encompassing spray ideal for everyday use
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- This product can help a building earn Water Efficiency points in LEED® Green Building Rating System

### Material

- KOHLER® finishes resist corrosion and tarnishing

### Installation

- Shower arm and flange sold separately
- Wall-mount
- 1/2 -14 NPT connection

### Recommended Products/Accessories

- K-7395 Shower Arm and Flange
- K-7397 Shower Arm and Flange
- K-23723 Faucet cleaner



### Codes/Standards






ASME A112.18.1/CSA B125.1  
DOE - Energy Policy Act 1992  
EPA WaterSense®  
California Energy Commission (CEC)  
IAPMO Certification



### KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	SN	Vibrant® Polished Nickel
	BN	Vibrant® Brushed Nickel
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne Brass



**Technical Information**

All product dimensions are nominal.

Drain included: No

**Showerhead/Body Spray:**

Rated maximum flow: 1.75 gal/min (6.6 l/min)

**Notes**

Install this product according to the installation guide.