

## Features

- Clear glass shades with inner frosted glass diffusers for reduced glare
- Requires bulb with medium (E26) base; T10 bulb recommended (sold separately)
- Coordinates with faucets and accessories in the Artifacts collection
- Suitable for damp locations, per UL 1598

## Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

## Installation

- For installation as a downlight only

## Recommended Products/Accessories

K-23723 Faucet cleaner



## Codes/Standards

UL 1598  
CSA C22.2 No. 250.0  
cETL Listed  
ETL Listed



## KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	SNL	Polished Nickel
	TTL	Titanium
	BNL	Brushed Nickel
	CPL	Polished Chrome
	BLL	Matte Black
	2GL	Brushed Moderne Brass
	BVL	Brushed Bronze
	AFL	French Gold



### Required Electrical Service

0.333 A

### Technical Information

All product dimensions are nominal.

Material:	Brass, Glass, Zinc
Number of Lights:	1
Lighting Type:	Socket-based
Socket Type:	E-26 Medium
Number of Shades:	1
Shade Type:	Clear Glass
Hanging Type:	Adjustable pulley

### Notes

Install this product according to the installation instructions.