

Features

- Single joystick lever handle is simple to use and makes adjusting water temperature easy
- 4-15/16" (125 mm) spout reach
- 3-3/10" (85 mm) spout height
- Aerated flow delivers a smooth, steady stream of water
- Red/blue indexing
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- Includes valve
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- Clicker drain with tailpiece
- Coordinates with Stance faucets, accessories, and showering components to complete your bathroom

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For single-hole installation
- Flexible supply lines simplify installation

Recommended Products/Accessories


K-23723 Faucet cleaner



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 4-15/16" (126 mm)

Notes

Install this product according to the installation instructions.