

KOHLER[®] Faucets

Bath and shower faucet with Knob handles, 8.7 lpm

Stance™
K-72844T-9

Features

- Features integrated 35 mm mixing valve
- 1/4-turn full brass ceramic valve
- Two knob handles control on/off function and volume and temperature
- Red/blue indexing
- 10.0 gpm (37.9 lpm) maximum flow rate at 45 psi (3.1 bar)
- Diverter spout
- Rainduet™ handshower provides three spray experiences: full coverage with Katalyst™ air-induction technology, Champagne, and massage
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Thumb tab allows for a smooth transition between sprays
- Includes 59" (1500 mm) shower hose and holder
- 2.3 gpm (8.7 lpm) maximum handshower flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.

Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing


Installation

- Wall-mount
- G 1/2 inlet connection

KOHLER Faucets

Bath and shower faucet with Knob handles, 8.7 lpm

Stance™
K-72844T-9



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 10 gal/min (37.9 l/min)

Drain included: No

Spout:

Spout reach: 8-3/16" (208 mm)

Handshower:

Rated maximum flow: 2.3 gal/min (8.7 l/min)