

### Features

- Features integrated 35 mm mixing valve
- 1/4-turn full brass ceramic valve
- Two knob handles control on/off function and volume and temperature
- Red/blue indexing
- Rainduet™ handshower provides three spray experiences: full coverage with Katalyst™ air-induction technology, Champagne, and massage
- Handshower features contemporary design
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Thumb tab allows for a smooth transition between sprays
- Includes 59" (1500 mm) shower hose and holder
- 2.3 gpm (8.7 lpm) maximum handshower flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance



### Codes/Standards

Plumbing Standards  
GB 18145

See website for detailed warranty information.

### Material



- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation

- Wall-mount
- G 1/2 inlet connection

### Recommended Products/Accessories

K-23723 Faucet cleaner



**Technical Information**

All product dimensions are nominal.

Drain included: No

**Handshower:**

Rated maximum flow: 2.3 gal/min (8.7 l/min)

**Notes**

Install this product according to the installation instructions.