

Features

- Quarter-turn washerless ceramic disc valves
- 8" (203 mm) rigid connections
- Variety of handle style options
- 5-1/4" (133 mm) gooseneck spout
- Less drain
- Vandal-resistant aerator
- 0.5 gpm (1.9 lpm) maximum flow rate at 60 psi (4.14 bar)

Material

- Brass
- Brass valve bodies

Required Products/Accessories

- [K-16012-2](#) Standard Handles for Widespread Base Faucet
or
[K-16012-3](#) Cross Handles for Widespread Base Faucet
or
[K-16012-4](#) Lever Handles for Widespread Base Faucet




Codes/Standards

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
California Energy Commission (CEC)

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet flow rate: 0.5 gal/min (1.9 l/min)

Spout:

Spout reach: 5-1/4" (133 mm)

Notes

Install this product according to the installation instructions.