



Triton® | K-7305-KNE

0.5 gpm centerset commercial bathroom sink base faucet with gooseneck spout and vandal-resistant aerator, requires handles, drain not included

Features

- Quarter-turn washerless ceramic disc valves
- Vandal-resistant aerator
- Variety of handle style options
- Less drain
- 0.5 gpm (1.9 lpm) maximum flow rate at 60 psi (4.14 bar)



Codes/Standards

ASME A112.18.1/CSA B125.1
 NSF/ANSI/CAN 372
 NSF/ANSI/CAN 61
 DOE - Energy Policy Act 1992
 California Energy Commission (CEC)
 NSF/ANSI/CAN 61|NSF/ANSI/CAN 372

Technical Information

All product dimensions are nominal.

Spout

Spout Reach: 5-1/4" (133 mm)

Flow Rate

Faucet Flow Rate: 0.5 gpm (1.9 l/min)

Material

- Brass
- Brass valve bodies

Recommended Products/Accessories

K-23723 Faucet cleaner

Required Products/Accessories


- K-16010-3 Cross handles for centerset base faucet
- or
- K-16010-4 Lever handles for centerset base faucet
- or
- K-16010-5 Wristblade lever handles for centerset base faucet

Warranty

See website for detailed warranty information.

KOHLER® One-Year Limited Warranty





Installation Notes

Install this product according to the installation instructions.

