

KOHLER® Faucets

Composed™

Single-handle bathroom sink faucet with Cylindrical handle, 7.5 lpm
K-73050IN-7

Features

- Sleek contemporary design
- Single Cylindrical handle allows for both volume and temperature control
- Red/blue indexing
- 5.9 inch (151 mm) spout reach
- 4.1 inch (104 mm) spout height
- Laminar flow
- 7.5 lpm (2.0 gpm) maximum flow rate at 3.0 bar (43.5 psi)
- Includes pop-up drain with lift rod and 1.25 inch (32 mm) tailpiece
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- G 1/2 connection

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For single-hole installation



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BRD	



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain tailpiece included: Yes

Spout:

Spout reach: 6" (152 mm)

Notes

Install this product according to the installation instructions.