

Features



- Single cylindrical handle allows for both volume and temperature control
- Red/blue indexing
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- 5-15/16" (151 mm) spout reach
- 4-1/16" (103 mm) spout height
- Laminar flow delivers a graceful stream of water
- 2.2 gpm (8.3 lpm) maximum flow rate at 60 psi (4.14 bar)
- Includes pop-up drain with 1-1/4" (32 mm) tailpiece
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with Composed faucets, accessories, and showering components to complete your bathroom
- G 3/8" connection

Material

- KOHLER® finishes resist corrosion and tarnishing
- Premium material construction for durability and reliability


Installation

- Deck-mount
- For single-hole installation
- Preattached flexible supply lines simplify installation

**Codes/Standards**

General Acceptance (GA)

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Pressure: 60 psi (4.1 bar)

Drain included: Yes

Spout:

Spout reach: 5-15/16\" (151 mm)

Notes

Install this product according to the installation instructions.