

KOHLER® Faucets

Single-handle bathroom sink faucet with Cylindrical handle, 7.6 lpm
Composed™
K-73050T-B7

Features

- Versatile, contemporary design
- Single Cylindrical handle allows for both volume and temperature control
- Red/blue indexing on handle
- 5-15/16" (151 mm) spout reach
- 2.0 gpm (7.6 lpm) maximum flow rate at 45 psi (3.1 bar)
- Laminar flow
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Includes cable pop-up drain with 1-1/4" (32 mm) tailpiece
- Coordinates with Composed faucets, accessories, and showering components to complete your bathroom

Material

- Premium metal construction for durability and reliability

Installation


- Single-hole installation



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.5 gal/min (5.7 l/min)

Drain included: Yes

Spout:

Spout reach: 5-15/16" (151 mm)

Notes

Install this product according to the installation instructions.