

KOHLER® Faucets

Composed™

Tall single-handle bathroom sink faucet with Joystick handle, 8.3 lpm

K-73053T-4

Features

- Joystick handle allows for both on/off actuation and temperature setting
- Red/blue indexing
- 8-1/2" (215 mm) faucet height
- 7-1/8" (181 mm) spout reach
- Tall height is ideal for vessel-style sinks
- Laminar flow delivers a graceful stream of water
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- Includes pop-up drain with lift rod and 1-1/4" (32 mm) tailpiece
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with Composed faucets, accessories, and showering components to complete your bathroom

Material

- KOHLER® finishes resist corrosion and tarnishing
- Premium metal construction for durability and reliability

Installation

- For single-hole installation
- Flexible supply connections for easy installation

Recommended Products/Accessories

K-23726 Drain treatment
K-23723 Faucet cleaner
K-73141 18" Towel Bar
K-73142 24" Towel Bar
K-73144 24" Double Towel Bar
K-73145 towel arm
K-73146 Double Robe Hook
K-73147 Pivoting toilet paper holder
K-73148 Vertical toilet paper holder




Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.

KOHLER Faucets **Composed™**

Tall single-handle bathroom sink faucet with Joystick handle, 8.3 lpm
K-73053T-4



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 7-1/8" (181 mm)

Notes

Install this product according to the installation instructions.