

KOHLER® Faucets

Composed™

Widespread bathroom sink faucet with Lever handles,
8.3 lpm
K-73060K-4

Features

- Two lever handles offer separate control of hot and cold water
- Red/blue indexing
- 5-15/16" (151 mm) spout reach
- Laminar flow delivers a graceful stream of water
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- Includes pop-up drain with 1-1/4" (32 mm) tailpiece
- UltraGlide™ valves with dry-stem technology are designed to eliminate common leak paths and provide smooth, effortless control
- Coordinates with Composed faucets, accessories, and showering components to complete your bathroom

Material


- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- For 8" – 16" (203 – 406 mm) centers
- Handles are preassembled on valves to simplify installation
- Quick-connect fittings make installation easy

Recommended Products/Accessories

K-23726 Drain treatment
K-23723 Faucet cleaner
K-73141 18" Towel Bar
K-73142 24" Towel Bar
K-73144 24" Double Towel Bar
K-73145 towel arm
K-73146 Double Robe Hook
K-73147 Pivoting toilet paper holder
K-73148 Vertical toilet paper holder




Codes/Standards

None Applicable

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Pressure: 45 psi (3.1 bar)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 5-15/16" (151 mm)

Notes

Install this product according to the installation instructions.