

**Features**

- Versatile, contemporary design
- Two cross handles offer separate control of hot and cold water
- Red/blue indexing on handles
- 8-1/2" (216 mm) spout reach
- Aerated flow
- Stationary spout
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- Clicker drain with tailpiece and overflow
- Coordinates with Composed faucets, accessories, and showering components to complete your bathroom
- Trim only, requires valve to complete installation

**Material**

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing


**Installation**

- Wall-mount

**Codes/Standards**

Plumbing Standards  
GB 18145

See website for detailed warranty  
information.



**Technical Information**

All product dimensions are nominal.

Faucet flow rate: 2.2 gal/min (8.3 l/min)

Drain included: Yes

**Spout:**

Spout reach: 8-1/2" (216 mm)

**Notes**

Install this product according to the installation instructions.