

### Features

- Single lever handle allows for both temperature and volume control
- 8-1/4" (210 mm) spout reach
- Diverter spout
- 9.0 gpm (34.0 lpm) maximum flow rate at 45 psi (3.1 bar)
- Includes Shift™ Ellipse wand multifunction handshower and 79" (2000 mm) shower hose
- Multifunction handshower offers full coverage and targeted massage spray settings
- Full Coverage with Katalyst™ air-induction technology delivers a drenching spray experience, ideal for rinsing shampoo from hair
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 2.5 gpm (9.5 lpm) handshower maximum flow rate at 80 psi (5.5 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with Composed faucets, accessories, and showering components to complete your bathroom

### Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation


- Deck-mount
- G 1/2 inlet connection
- Three-hole installation



### Codes/Standards

Plumbing Standards  
GB 18145

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 9.24 gal/min (35 l/min)

Drain included: No

Drain with overflow: No

#### Spout:

Spout reach: 8-1/4" (210 mm)

#### Handshower:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

### Notes

For use with automatic compensating valves rated at 2.5 gal/min (9.5 l/min) or less.

Install this product according to the installation instructions.