

Features

- Two Lever handles offer separate control of hot and cold water
- Nondiverter spout
- 8-1/4" (210 mm) spout reach
- 12 gpm (45.4 lpm) maximum flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with Composed faucets, accessories, and showering components to complete your bathroom

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Deck-mount

Recommended Products/Accessories

K-73141 18" Towel Bar
K-73142 24" Towel Bar
K-73144 24" Double Towel Bar
K-73145 towel arm
K-73146 Double Robe Hook
K-73147 Pivoting toilet paper holder
K-73148 Vertical toilet paper holder



Codes/Standards

Plumbing Standards
GB 18145


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	2MB	Vibrant® Brushed Moderne Brass
	TT	Vibrant Titanium



Technical Information

All product dimensions are nominal.

Faucet flow rate: 12 gal/min (45.4 l/min)

Spout:

Spout reach: 8-1/4" (210 mm)

Notes

Install this product according to the installation instructions.