

Features


- Features integrated 35 mm mixing valve
- Single lever handle allows for both volume and temperature control
- 12 gpm (45.4 lpm) maximum flow rate at 45 psi (3.1 bar)
- Diverter spout
- Rainduet™ handshower provides three spray experiences: full coverage with Katalyst™ air-induction technology, Champagne, and massage
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Thumb tab allows for a smooth transition between sprays
- 2.3 gpm (8.7 lpm) maximum handshower flow rate at 45 psi (3.1 bar)
- Includes 59" (1500 mm) shower hose and holder
- Coordinates with Composed faucets, accessories, and showering components to complete your bathroom
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation



- Wall-mount
- G 1/2 inlet connection



Codes/Standards

None Applicable

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Drain included: No