

### Features

- Features integrated 35 mm mixing valve
- Single lever handle allows for both volume and temperature control
- Red/blue indexing
- 12 gpm (45.4 lpm) maximum flow rate at 45 psi (3.1 bar)
- Diverter spout
- Rainduet™ handshower provides three spray experiences: full coverage with Katalyst™ air-induction technology, Champagne, and massage
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Thumb tab allows for a smooth transition between sprays
- Includes 59" (1500 mm) shower hose and holder
- 2.3 gpm (8.7 lpm) maximum handshower flow rate at 45 psi (3.1 bar)
- Coordinates with Composed faucets, accessories, and showering components to complete your bathroom
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance



### Codes/Standards

Plumbing Standards  
GB 18145



See website for detailed warranty information.

### Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

### Installation

- Wall-mount
- G 1/2 inlet connection



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 12 gal/min (45.4 l/min)

Drain included: No

#### Handshower:

Rated maximum flow: 2.3 gal/min (8.7 l/min)