

Features

- Two-handle gooseneck bathroom sink faucet
- 3-11/16" (94 mm) gooseneck spout with rosespray
- 7-5/16" (186 mm) wall-to-spout outlet
- 12 gpm (gallons per minute) maximum flow rate
- Lever handles with red/blue indexing (ADA-compliant with correct installation)
- Less drain
- Adjustable flanges
- External NPT connections

Material

- Brass

Installation

- Pairs with the Brockway wall-mounted wash sink

Recommended Products/Accessories

- K-3200 36" wall-mount utility sink
- K-3202 48" wall-mount utility sink
- K-3203 60" wall-mount utility sink
- K-23723 Faucet cleaner



Codes/Standards



ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
All applicable US Federal and State material regulations
IAPMO Certification


KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|---|------|-----------------------|
|  | CP | Polished Chrome |
|  | SR | Vibrant Bright Nickel |



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 12 gal/min (45.4 l/min)

Drain included: No

Spout:

Spout reach: 3-11/16" (93 mm)

Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

Notes

Install this product according to the installation instructions.