

### Features

- Quarter-turn washerless ceramic disc valves
- Variety of handle style options
- 12" (305 mm) rigid connections
- 5-1/4" (133 mm) gooseneck spout
- Less drain
- 0.5 gpm (1.9 lpm) maximum flow rate at 60 psi (4.14 bar)

### Material

- Brass
- Brass valve bodies

### Required Products/Accessories

[K-16012-2](#) Standard Handles for Widespread Base Faucet

or

[K-16012-3](#) Cross Handles for Widespread Base Faucet

or

[K-16012-4](#) Lever Handles for Widespread Base Faucet

or

[K-16012-5](#) Wristblade Handles for Widespread Base Faucet

### Recommended Products/Accessories

K-23723 Faucet cleaner

### Optional Products/Accessories

1160594 .35 gpm Aerator, Large



### Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

All applicable US Federal and State material regulations


DOE - Energy Policy Act 1992

California Energy Commission (CEC)

IAPMO Certification

### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

### Faucet:

Flow rate: 0.5 gal/min (1.9 l/min)

Drain included: No

### Spout:

Spout reach: 5-1/4" (133 mm)

## Notes

Install this product according to the installation guide.