

Features

- Sleek, minimalist design
- Tall height is ideal for vessel-style sinks
- Single Cylindrical handle allows for both volume and temperature control
- 8 inch (203 mm) spout height
- 7.13 inch (181 mm) spout reach
- Laminar flow
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- Includes pop-up drain
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Deck-mount
- Single-hole mounting
- Preattached flexible supply lines simplify installation

Recommended Products/Accessories

K-23726 Drain treatment



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BRD	



Technical Information

All product dimensions are nominal.

Faucet flow rate: 2.2 gal/min (8.3 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 7-1/8" (181 mm)

Notes

Install this product according to the installation instructions.