

Features

- Versatile, contemporary design
- Single handle provides on/off activation, volume, and temperature control
- Red/blue indexing on handle
- 7-1/8" (181 mm) spout reach
- 8-1/16" (205 mm) spout height
- Aerated flow
- Stationary spout
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Clicker drain with tailpiece and overflow
- Coordinates with Composed faucets, accessories, and showering components to complete your bathroom

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing


Installation

- Preattached flexible supply lines simplify installation
- Single hole

**Codes/Standards**

Plumbing Standards
GB 18145

See website for detailed warranty
information.



Technical Information

All product dimensions are nominal.

Faucet flow rate: 2.2 gal/min (8.3 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 7-1/8" (181 mm)