

### Features

- Modern, simplistic exposed thermostatic valve serves as a hub for shower controls
- Thermostatic valve allows user to set and maintain precise temperature
- Red/blue indexing
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- Antiscald protection
- Volume control valve provides on/off operation, along with precise control of water volume and intensity
- Rainduet™ handshower provides three spray experiences: full coverage with Katalyst™ air-induction technology, Champagne, and massage
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Includes 59" (1500 mm) shower hose and holder
- 2.3 gpm (8.7 lpm) maximum handshower flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with Composed faucets, accessories, and showering components to complete your bathroom

### Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Technology

- Thermostatic technology automatically maintains temperature within +/- 0.4°C (+/- 0.72°F) during water pressure fluctuations

### Installation


- Wall-mount
- G 1/2 inlet connection



### Codes/Standards

Plumbing Standards  
QB/T 2806

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Drain included: No

### Handshower:

Rated maximum flow: 2.3 gal/min (8.7 l/min)