

### Features

- Unique square 7.87 inch (200 mm) single-function rainhead creates a modern look
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Optimized sprayface for maximum performance
- 2.3 gpm (8.7 lpm) maximum flow rate at 43.5 psi (3.0 bar)

### Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Technology

- Katalyst™ air-induction technology infuses water with air, creating bigger drops for a more powerful spray

### Installation

- G 1/2 (13 mm) inlet connection
- Ceiling- or wall-mount



### Codes/Standards


None Applicable

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome



### Technical Information

All product dimensions are nominal.

#### Showerhead/Body Spray:

Rated maximum flow: 2.4 gal/min (9.1 l/min)

### Notes

Install this product according to the installation guide.