



Triton® | K-7320-4

Double lever handle utility sink faucet with gooseneck spout

Features

- Valvet® valves
- Adjustable flanges
- Stationary gooseneck spout
- Lever handles
- 5-3/16" (132 mm) spout reach
- 1/2" NPT inside-threaded inlets
- Lower flow aerator options are available
- 2.2 gpm (8.3 lpm) maximum flow rate at 60 psi (4.14 bar)



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-30-2026 01:21 - US-CA

THE BOLD LOOK
OF **KOHLER**®

Codes/Standards

ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

ADA CSA B651

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 372
NSF/ANSI/CAN 61
NSF/ANSI/CAN 61|NSF/ANSI/CAN 372
ADA
ICC/ANSI A117.1
CSA B651

Technical Information

All product dimensions are nominal.

Handle

Handle Style/Type: Lever

Spout

Spout Reach: 5-3/16" (132 mm)

Flow Rate

Faucet Flow Rate: 2.2 gpm (8.3 l/min)

Material

- Brass
- Brass valve bodies

Recommended Products/Accessories

K-23726 Drain treatment

K-23723 Faucet cleaner


Warranty

See website for detailed warranty information.

KOHLER® Faucet Lifetime Limited Warranty



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-30-2026 01:21 - US-CA



Installation

- For 8" (203 mm) centers

Installation Notes

Install this product according to the installation instructions.

ADA compliant for faucet handles only
 ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

